PASSIONATE VISION

P 25⁺ BUILDING A NEW VIEW OF POSSIBILITY

World class capability


See your world in a new way through seamless equipment that builds your passion. Explore the possibilities with one hour noise-free exposures, superior ISO 800 capture, Live Preview, color in even the darkest areas and new levels of detail in highlights and shadows. Let OptiColor⁺, Dynamic⁺ and XPose⁺ redefine your creative limits.

Your Phase One P 25⁺ never becomes obsolete

Your digital investment is protected through Phase One's unique upgrade program. We also offer a 3-year warranty and 24 hour unit replacement guarantee so you can feel secure and always meet tight deadlines. When you're the artist and the entrepreneur, your main focus is always photography and fast project turnaround. We are here to make it happen...

PHASE ONE passion & profit







SPECIFICATIONS:

.

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

Imaging technology		
CCD:	Full frame CCD	
Lens Factor:	1.1	
Resolution:	22 mega pixels	
Active pixels:	5436 x 4080 pixe	
CCD size effective:	48.9 x 36.7 mm	
Pixel size:	9 x 9 micron	
Image ratio:	4:3	
Microlens on CCD:	No	
Antiblooming:	10 f-stops	
Dynamic range:	12 f-stops	

Storage files

Phase Ones IIQ RAW file format speeds the image capture and file transfer. Incre the storage capacity by turning the full 1 image data into a compact RAW file form The default IIQ RAW-large format is com lossless.

17 MB

25 MB

16 bit per color

llQ	small:	
llQ	large:	

Output files

Color depth:

	Image file formats:	TIFF-RGB, TIFF-CMYK,	LCD screen	
		JPEG	Size:	2.2"
	Color management:	RGB, Embedded ICC	Resolution:	230,4
		profile, CMYK	Viewing angle:	160°
S				
	Sensitivity		Models of P ⁺ bac	k mou
	ISO:	50, 100, 200, 400, 800	Phase One H101:	Hass
			Hasselblad V:	Hass
	Camera system			533E
	Capture time:	1.5 sec./frame		501C
	Storage security:	Phase One 3S technology		Marr
		- Secure Storage System		RZ67
	Battery type:	7.2 V Lithium Ion	Mamiya 645:	Marr
up		2500mAh		645A
eases	Battery lifetime:	4000 captures/4 hours	Contax 645:	Cont
6 bit	Exposure time:	1/10,000 sec. up to 1 hour		
nat.		with XPose ⁺ technology	Technical & large	forma
pletely	Live preview:	Yes	Wide angle:	Hass
	IR filter:	Mounted on CCD		Hors
	Cooling system:	Passive cooling and		of ac
		sleeping architecture		supp
	Power up time:	Less than 2 sec.	4" x 5":	Arca
	Power:	8-33 V DC		Rolle
		(from FireWire®)		M679

e:	2.2"
solution:	230,400 pixels
wing angle:	160°

s of P ⁺ back mounts		
)ne H101:	Hasselblad H1 and H2	
lad V:	Hasselblad 555ELD,	
	533ELX, 503CW and	
	501CM	
	Mamiya RB67 and	
	RZ67 Pro II	
645:	Mamiya 645AFD,	
	645AFDII, RZ67 Pro IID	
645:	Contax 645AF	

at camera support

selblad 903 SWC. seman SW-D & range dapters with 35 mm port a Swiss. Cambo 4x5. ei Xact. Linhof 79/4x5, Toyo, Sinar, Plaubel. Horseman

Operating conditions Temperature: 0° to 40°C (32° to 122°F) Humidity: 15 to 80% RH (non-condensing) Lighting Supports all photographic lights: Flash, tungsten, daylight, fluorescent, HMI **Computer minimum requirements** G4, 500 MB RAM, Mac: FireWire® interface. Mac OSX PC: Pentium III, 500 MB RAM IEEE 1394 interface. Windows XP/2000 Software

.....

.....

........

.

.....

.

.

.....

.

.

.

.

.

.

........

........

.

.....

.....

.....

.....

.....

.....

.....

Capture One DB or Capture One Pro

Certifications

CE

Phase One A/S Roskildevej 39 DK-2000 Frederiksberg Denmark Tel.: +45 36 46 01 11 Fax: +45 36 46 02 22 Email: info@phaseone.dk
 Phase One Germany

 Oskar-Jäger-Str. 160

 D-50825 Köln

 Germany

 Tel.: +49 (0)221 54 02 26 - 0

 Fax: +49 (0)221 45 02 26 - 22

 Email: info@phaseone.de

....

Phase One Inc.

200 Broadhollow Road (Suite 312) Melville, NY 11747 - 0983 USA Tel.: +1 631 547 8900 Fax: +1 631 547 9898 Email: info@phaseone.com Phase One Asia 1177 Nong, No 16 - 1802 Yong Shi Pu Lu Shanghai, 200082 China Tel.: +86 2163842854 Fax: +86 2155217747 Email: Izm@phaseone.com

www.phaseone.com

Phase One support: http://support.phaseone.com



